

## TECHNICAL DATA SHEET

# DUBL CHEK CP-2

## White Contrast Paint

Code 1504

### DESCRIPTION

DUBL-CHEK CP-2 is a specially formulated, fast drying, low odour white paint that provides a high contrast background for interpreting magnetic particle results. CP-2 enhances the visibility of indications under visible light conditions when the background material has a similar colour to the particles. When dry, CP-2 is resistant to wet suspension fluids, but is easily removed with DUBL-CHEK DR-64.

### FEATURES & BENEFITS

- A unique 360° spray valve
- High contrast, fast drying and low odour
- Multiple spray patterns for controlled application and comfort
- Aerosols offer convenience and portability
- More coverage for every application
- Solvent removable

### COMPANION DUBL-CHEK PRODUCTS

DUBL-CHEK BO-1

### DIRECTIONS

**Note:** These instructions describe the basic process, but they may need to be amended by the user to comply with applicable specifications and/or inspection criteria provided by the contracting agency.

1. Clean the test surface and allow it to dry.
2. The longer CP-2 is stirred or agitated the more uniform the spray.
3. Apply a thin coat of CP-2 contrast paint to the inspection area from approximately 150mm from the surface.
4. Wait approximately 20 seconds, depending of ambient temperature, for the paint to dry.
5. Magnetise the area to be inspected.
6. Ensure continuous agitation of the suspension fluid. If using an aerosol, shake vigorously before and during inspection.
7. Apply the suspension to the test part.
8. Allow the excess oil/water to run off the inspection area.
9. Inspect the surface under visible light.
10. Collections of particles will reveal discontinuities at the leakage fields.
11. Clean and repeat the process; changing the orientation of the magnetising direction.



## TECHNICAL DATA SHEET

### PHYSICAL PROPERTIES

Colour:	White
Odour:	Low residual smell
Aerosol Coverage:	Approx. 60 linear meters
Temperature limit:	4°C to 50°

### ORDERING INFORMATION

Product Code	Packaging
1504/400	Aerosol
1504/42	3.8 liters (1 gallon)
1504/51	18.9 liters 5 gallons)

### SPECIFICATIONS COMPLIANCE

- ASME Boiler and Pressure Vessel Code Section V
- ASTM E709
- ASTM E3024
- AS 1171
- ISO 9934

### STORAGE/SHELF LIFE

Keep away from moisture and sunlight. Keep the container closed when not in use. Refer to NDT Shelf Life and Storage Recommendations for further information.

### BATCH NUMBERS

Batch numbers can be found on the bottom of aerosol cans or labels of bulk containers. Certificate of Conformance documents are provided with the product or can be download from [www.callington.com](http://www.callington.com)

### HEALTH & SAFETY

UBL-CHEK CP-2 is flammable and when packaged within an aerosol is extremely flammable. Use with adequate ventilation and away from spark, fire or open flames. Avoid prolonged or repeated contact with skin. Do not breathe gas, fumes, vapour or spray. Consult the MSDS for more Safety and Health information.

Get medical attention if irritation develops and persists. Ensure that medical personnel are aware of the material(s) involved and take precautions to protect themselves.

**WARRANTY** – All statements, information and data presented herein are believed to be accurate and reliable but are not to be taken as a guarantee, expressed or implied, for which seller assumes legal responsibility and they are offered solely for your consideration, investigation and verification. Statements or suggestions concerning possible use of this product are made without representation or warranty that any such use is free of patent infringement and are not recommendations to infringe on any patent.  
Created 3<sup>rd</sup> September 2020 Date Printed 10/10/2023 11:14 AM